



Click [here](#) for the 3D model.

General Information

Series	SU-9H
Style	Through-Hole Bobbin
RoHS	Yes
Miscellaneous	Temperature Rise Maximum: 40 K.
Core	Mn-Zn Ferrite

Specifications

Voltage AC	250 VAC
Inductance	800 uH
Rated Current	1 A
Temperature Range	-25/+120°C
DC Resistance	0.3 Ohms

Dimensions

L	17mm MAX
T	15.5mm MAX
H	12.5mm MAX
LL	4mm MIN
S	8mm +/-0.5mm
S1	7mm +/-0.5mm
Wire Size	0.27mm
F	0.6mm NOM

Packaging Specifications

Packaging	Tray
Packaging Quantity	1000
Typical Component Weight	3.4 g