




General Information

Series	T266 CSS21
Dielectric	MnO2 Tantalum
Style	Axial Hermetic
Description	Axial, Solid Tantalum, Hermetically Sealed, Military, CSS21 Style
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - http://www.p65warnings.ca.gov .
Termination	Lead (SnPb)
Lead	Wire Leads
Qualifications	CSS21
AEC-Q200	No
Construction	Hermetic

Specifications

Capacitance	120 uF
Capacitance Tolerance	10%
Voltage DC	10 VDC (85C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	8% 1kHz 25C
Failure Rate	B (0.1%/1000 Hrs)
ESR	0.1 Ohms (100kHz)
Leakage Current	6 uA

Dimensions

D	7.09mm +0.41/-0.38mm
L	16.51mm +/-0.79mm
L2	20.88mm MAX
LL	38.1mm +/-6.35mm
F	0.64mm +/-0.05mm

Packaging Specifications

Packaging	Tray
Packaging Quantity	20