
UB2-12SNU

KEMET, UB2, Relays, Signal





General Information	
Series	UB2
Style	SMD
Description	Miniature Signal Relay, Single Coil Latch
Features	Super-Compact Size, Flat- Package
RoHS	Yes
Coil Type	Single Coil (Latching)
Coil Type	Single Coil (Latching)

Click here for the 3D model.

Dimensions	
Н	8.8mm MAX
L	10.6mm +/-0.3mm
W	5.7mm +/-0.3mm
LL	1mm NOM
S	3.2mm +/-0.15mm
S1	2.2mm +/-0.15mm
F	0.8mm +/-0.1mm
F1	3.1mm +/-0.1mm

Packaging Specifications		
Packaging	Tube	

-40/+85°C	
12 V	
2 Form C (DPDT)	
1A	
1440 Ohms +/-10%	
Silver alloy with gold alloy overlay	
9 (Set/Reset)	
100 mW	
30 W, 37.5 VA	
220 V	
250 VAC	
>10A	
1Amps	
100 mOhms	
Approximately 2ms	
Approximately 1ms	
1GOhms	
1000 VAC (1min) 1500 V Surge	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO