


FAHAV3100ZC

KEMET, FAH, EMI/RFI Filters, Noise Suppression, 250 VAC, 1.6 A, 45x28x17mm



Click [here](#) for the 3D model.

Dimensions	
L	45mm NOM
W	28mm NOM
H	17mm NOM
S	10.2mm NOM

Packaging Specifications	
Packaging	Bulk
Packaging Quantity	1

General Information	
Series	FAH
Style	Plastic Box
Description	Suppression Filter, Compact, High Performance
Phase	Single-phase
RoHS	Yes
Qualifications	IEC/EN 60939, CSA
Terminal Type	Tab Leads

Specifications	
Voltage AC	250 VAC
Rated Frequency	50-60 Hz
Rated Current	1.6 A (40°C)
Rated Temperature	40°C
Temperature Range	-25/+100°C
Climate Category	25/085/21
Test Voltage DC (P to P)	1700 VDC
Test Voltage DC (P to E)	3000 VDC
Leakage Current	0.26 mA (MAX)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.