



Specifications	
Voltage AC	440 VAC
Voltage DC	750 VDC
Rated Frequency	50-60 Hz
Rated Current	40 A
Ripple Current	40 A
Rated Temperature	40°C
Temperature Range	-40/+85°C
Climate Category	40/085/56

Dimensions	
A	39.5mm MIN
B	166mm MIN
D1	Threaded Studs M6
Packaging Specifications	
Packaging	Bulk
Packaging Quantity	1

© 2006 - 2025 YAGEO