




HV RAD-LDD Indust X7R HV, Ceramic, 0.22 uF, 10%, 500 VDC, X7R, Radial Leaded Multilayer Ceramic Capactor, 6.99 mm



Click here for the 3D model.

| General Information | |
|-------------------------|--|
| Series | HV RAD-LDD Indust X7R HV |
| Style | Radial |
| Description | Radial Leaded Multilayer Ceramic Capactor |
| RoHS | No |
| Prop 65 | WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov / |
| SCIP Number | ef26097b-3862-4ee0-b0ad-40 4a563ece0f |
| Termination | Copper |
| Lead | Wire Leads |
| Testing and Reliability | MIL-PRF-49467 Group A |
| Qualifications | MIL-PRF-49467 Group A |
| AEC-Q200 | No |

| Dimensions | |
|------------|-------------------------|
| L | 9.4mm MAX |
| Н | 7.62mm MAX |
| Т | 6.35mm MAX |
| S | 6.99mm +/-0.762mm |
| LL | 31.75mm MIN |
| F | 0.635mm +0.102/-0.051mm |

| Packaging Specifications | |
|--------------------------|--------------|
| Packaging | Waffle, Tray |
| Packaging Quantity | 28 |

| 0.22 uF |
|---------------------|
| 10% |
| 500 VDC |
| 750 VDC |
| -55/+125°C |
| X7R |
| 15%, 1kHz 1.0Vrms |
| 2.5% 1 kHz 1.0Vrms |
| 2% Loss/Decade Hour |
| 100 GOhms |
| |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/05/2025 © 2006 - 2025 YAGEO