




RAD-LDD Indust COG HT200C, Ceramic, 100 pF, 5%, 200 VDC, COG, High Temp, 200C, Radial Molded, Gold Termination, Industrial Grade, 5.08 mm



Click	here	for	the	3D	model.
CIICK	nere	101	uie	Sυ	model

General Information	
Series	RAD-LDD Indust COG HT200C
Style	Radial
Description	High Temp, 200C, Radial Molded, Gold Termination, Industrial Grade
Features	Commercial
RoHS	With Exemptions
REACH	SVHC (Pb - CAS 7439-92-1)
SCIP Number	e1a5b9fc-0de5-4ce0-a6ef-55df 071d82eb
Termination	Gold
Lead	Formed
AEC-Q200	No
Halogen Free	Yes
Typical Component Weight	493 mg

Dimensions	
L	4.83mm +/-0.25mm
Н	5.97mm +/-0.25mm
Т	2.29mm +/-0.25mm
S	5.08mm +/-0.38mm
LL	31.75mm MIN
F	0.635mm +0.102/-0.051mm
G	1.14mm MAX
K	4.83mm +/-0.25mm

Packaging Specifications		
Packaging	T&R, 305mm	
Packaging Quantity	500	

Specifications	
Capacitance	100 pF
Tolerance	5%
Voltage DC	200 VDC
Dielectric Withstanding Voltage	250 VDC
Temperature Range	-55/+200°C
Temp. Coefficient	COG
Dissipation Factor	2.5%
Aging Rate	0% Loss/Decade Hour
Insulation Resistance	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/30/2025 © 2006 - 2025 YAGEO