

C1808X471KGRALTU

Aliases (C1808X471KGRAL7800)

SMD Comm X7R HV Flex, Ceramic, 470 pF, 10%, 2,000 VDC, X7R, SMD, MLCC, FT-CAP, Temperature Stable, 1808, 2.9 mm



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Series | SMD Comm X7R HV Flex |
| Style | SMD Chip |
| Description | SMD, MLCC, FT-CAP, Temperature Stable |
| Features | FT-CAP, Temperature Stable |
| RoHS | No |
| Prop 65 | WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/ |
| Termination | Flexible Termination With Lead (SnPb) |
| Marking | No |
| AEC-Q200 | No |
| Typical Component Weight | 100 mg |
| Shelf Life | 78 Weeks |
| MSL | 1 |

Specifications

| | |
|--------------------------------------------------------------------|-------------------------------------------------|
| Capacitance | 470 pF |
| Measurement Condition | 1 kHz 1.0Vrms |
| Tolerance | 10% |
| Voltage DC | 2000 VDC |
| Dielectric Withstanding Voltage | 2,400 VDC |
| Temperature Range | -55/+125°C |
| Temp. Coefficient | X7R |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 15%, 1kHz 1.0Vrms |
| Dissipation Factor | 2.5% 1 kHz 1.0Vrms |
| Aging Rate | 3% Loss/Decade Hour: Referee Time is 1000 Hours |
| Insulation Resistance | 100 GOhms |

Dimensions

| | |
|-----------|-----------------|
| Chip Size | 1808 |
| L | 4.7mm +/-0.5mm |
| W | 2mm +/-0.2mm |
| T | 1.6mm +/-0.15mm |
| S | 2.9mm MIN |
| B | 0.7mm +/-0.35mm |

Packaging Specifications

| | |
|--------------------|--------------------------|
| Packaging | T&R, 180mm, Plastic Tape |
| Packaging Quantity | 1000 |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.