


# C1812C333KFRACTU

Aliases (C1812C333KFRAC7800) SMD Comm X7R HV, Ceramic, 0.033 uF, 10%, 1,500 VDC, X7R, SMD, MLCC, High Voltage, Temperature Stable, 1812, 2.3 mm



| General Information      |  |
|--------------------------|--|
| Series                   | SMD Comm X7R HV                                |
| Style                    | SMD Chip                                       |
| Description              | SMD, MLCC, High Voltage,<br>Temperature Stable |
| Features                 | High Voltage                                   |
| RoHS                     | Yes  |
| Termination              | Tin  |
| Marking                  | No   |
| AEC-Q200                 | No   |
| Typical Component Weight | 185 mg   |
| Shelf Life               | 78 Weeks                                       |
| MSL                      | 1  |

| Dimensions |                 |
|------------|-----------------|
| Chip Size  | 1812            |
| L          | 4.5mm +/-0.3mm  |
| W          | 3.2mm +/-0.3mm  |
| Т          | 2.5mm +/-0.20mm |
| S          | 2.3mm MIN       |
| В          | 0.6mm +/-0.35mm |
|            |                 |

| W                        | 3.2mm +/-0.3mm           | Tolerance                                     | 10%                |
|--------------------------|--------------------------|---|--------------------|
| Т                        | 2.5mm +/-0.20mm          | Voltage DC                                    | 1500 VDC           |
| S                        | 2.3mm MIN                | Dielectric Withstanding Voltage               | 1,800 VDC          |
| В                        | 0.6mm +/-0.35mm          | Temperature Range                             | -55/+125°C         |
|                          |                          | Temp. Coefficient                             | X7R                |
| Packaging Specifications |                          | Capacitance Change with                       | 15%, 1kHz 1.0Vrms  |
| Packaging                | T&R, 180mm, Plastic Tape | Reference to +25°C and 0 VDC<br>Applied (TCC) |                    |
| Packaging Quantity       | 500                      | Dissipation Factor                            | 2.5% 1 kHz 1.0Vrms |
|                          |                          |   |                    |

| Specifications   |  |
|--|--|
| Capacitance  | 0.033 uF   |
| Measurement Condition  | 1 kHz 1.0Vrms                                      |
| Tolerance  | 10%  |
| Voltage DC   | 1500 VDC   |
| Dielectric Withstanding Voltage  | 1,800 VDC  |
| Temperature Range  | -55/+125°C   |
| Temp. Coefficient  | X7R  |
| Capacitance Change with<br>Reference to +25°C and 0 VDC<br>Applied (TCC) | 15%, 1kHz 1.0Vrms                                  |
| Dissipation Factor   | 2.5% 1 kHz 1.0Vrms                                 |
| Aging Rate   | 3% Loss/Decade Hour: Referee<br>Time is 1000 Hours |
| Insulation Resistance  | 3.0303 GOhms                                       |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 10/29/2025 © 2006 - 2025 YAGEO




# C1812C333KFRACTU

Aliases (C1812C333KFRAC7800) SMD Comm X7R HV, Ceramic, 0.033 uF, 10%, 1,500 VDC, X7R, SMD, MLCC, High Voltage, Temperature Stable, 1812, 2.3 mm

### **Simulations**

-55.0

For the complete simulation environment please visit Y-SIM.



Generated 10/29/2025 © 2006 - 2025 YAGEO

0.0

200.0

400.0

800.0

Voltage (VDC)

-80.0

10.0 k 100.0 k 1.0 M 10.0 M 100.0 M 1.0 G

Frequency (Hz)



### C1812C333KFRACTU

Aliases (C1812C333KFRAC7800) SMD Comm X7R HV, Ceramic, 0.033 uF, 10%, 1,500 VDC, X7R, SMD, MLCC, High Voltage, Temperature Stable, 1812, 2.3 mm

#### These are simulations.

This is not a specification!

The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

The responses shown do not represent a specified or implied maximum capability of the device for all applications.

- The ESR used for ripple "Ripple Current/Voltage vs. Frequency" plots is the ESR at ambient temperature.

- The ESR in the "Temperature Rise vs. Ripple Current" plots is the ESR at ambient temperature. The ESR in the "Temperature Rise vs. Ripple Current" plots is adjusted to each incremental temperature rise before the power and ripple current is calculated. The effects shown herein are based on measured data from a multiple part sample of the parts in question. Ripple capability of this device will be factored by thermal resistance (Rth) created by circuit traces (addi affects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

  The peak voltages generated in the "Temperature Rise vs. Combined Ripple Currents" plot are calculated for each frequency and are not combined with voltages
- generated at any other harmonics.

  Please consult with the catalog or field applications engineer for maximum capability of the device in specific applications.

All product information and data (collectively, the "Information") are subject to change without notice.

KEMET K-SIM is designed to simulate behavior of components with respect to frequency, ambient temperature, and DC bias levels. The responses shown represent the typical response for each part type. Specific responses may vary, depending on manufacturing variation effects of all parameters involved, including the specified tolerances applied to capacitance and unspecified variations of ESR, ESL, and leakage resistance.

All Information given herein is believed to be accurate and reliable, but is presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

If you have any questions please contact K-SIM.

Generated 10/29/2025 © 2006 - 2025 YAGEO