




 $\hbox{GoldMax 300 Comm X7R HV, Ceramic, 0.01 uF, 20\%, 1,000 VDC, X7R, GoldMax, Commercial Standard, 5.08 mm } \\$ 



| General Information |                              |
|---------------------|------------------------------|
| Series              | GoldMax 300 Comm X7R HV      |
| Style               | Radial                       |
| Description         | GoldMax, Commercial Standard |
| RoHS                | Yes                          |
| Termination         | Tin                          |
| Lead                | Formed                       |
| Failure Rate        | N/A                          |
| AEC-Q200            | No                           |
| Halogen Free        | Yes                          |

Click here for the 3D model.

| Dimensions |                      |
|------------|----------------------|
| L          | 5.08mm MAX           |
| Н          | 7.62mm MAX           |
| Т          | 3.81mm MAX           |
| S          | 5.08mm +/-0.78mm     |
| LL         | 7mm MIN              |
| F          | 0.51mm +0.1/-0.025mm |
|            |                      |

| Packaging Specifications |           |  |
|--------------------------|-----------|--|
| Packaging                | Bulk, Bag |  |
| Packaging Quantity       | 500       |  |

| Specifications   |  |
|--|--|
| Capacitance  | 0.01 uF  |
| Measurement Condition  | 1 kHz 1.0Vrms                                      |
| Tolerance  | 20%  |
| Voltage DC   | 1000 VDC   |
| Dielectric Withstanding Voltage  | 1,200 VDC  |
| Temperature Range  | -55/+125°C   |
| Temp. Coefficient  | X7R  |
| Capacitance Change with<br>Reference to +25°C and 0 VDC<br>Applied (TCC) | 0.15, 1kHz 1.0Vrms                                 |
| Dissipation Factor   | 2.5% 1 kHz 1.0Vrms                                 |
| Aging Rate   | 3% Loss/Decade Hour: Referee<br>Time is 1000 Hours |
| Insulation Resistance  | 100 GOhms  |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/05/2025 © 2006 - 2025 YAGEO