



Click [here](#) for the 3D model.

Dimensions

L	19.56mm MAX
H	18.29mm MAX
T	6.89mm MAX
S	17.15mm +/-0.762mm
LL	31.75mm MIN
F	0.635mm +0.102/-0.051mm

Packaging Specifications

Packaging	Waffle, Tray
Packaging Quantity	20

General Information

Series	HV RAD-LDD Indust X7R HV
Style	Radial
Description	Radial Leaded Multilayer Ceramic Capacitor
RoHS	No
Prop 65	⚠ WARNING: Cancer and reproductive harm - http://www.p65warnings.ca.gov .
SCIP Number	ef26097b-3862-4ee0-b0ad-404a563ece0f
Termination	Copper
Testing and Reliability	MIL-PRF-49467 Group A
Qualifications	MIL-PRF-49467 Group A
AEC-Q200	No

Specifications

Capacitance	0.015 uF
Capacitance Tolerance	10%
Voltage DC	5000 VDC
Dielectric Withstanding Voltage	6000 VDC
Temperature Range	-55/+125°C
Temperature Coefficient	X7R
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	15%, 1kHz 1.0Vrms
Dissipation Factor	2.5% 1 kHz 1.0Vrms
Aging Rate	2% Loss/Decade Hour
Insulation Resistance	100 GOhms