Hybrid Radial Crown Capacitors PHH223, +125°C, Hybrid Radial Crown, UL ESR, AEC-Q200





Overview

KEMET's PHH223 is a Ultra Low ESR conductive polymer hybrid capacitor with outstanding electrical performance. These capacitors contain a radial crown, which allows them to be mounted in a standing position. The device has a polarized all-welded design, tinned copper wire leads, and a negative pole connected to the case. The PHH223 winding is housed in a cylindrical aluminum can with a high purity aluminum lid and high-quality rubber gasket. Low ESR is conditioned by a highly conductive polymer (PEDOT/PSS) and an all-welded design. The polymer system creates an electrical pathway between the anodic oxide layer and the cathode through a mechanical separator - paper. The PHH223 winding is impregnated with liquid electrolyte that results to self-healing features of the capacitor. Thanks to its mechanical robustness, the PHH223 is suitable for use in mobile and automotive installations with operation up to +125°C.

Applications

KEMET's PHH223 is a series of high performance radial crown hybrid capacitors. It is designed for automotive applications with extremely high demands.

Benefits

- 8,000 hours at +125°C
- · High temperature capability up to 140°C
- · Extremely high ripple current
- Up to 46 Arms, continuous load
- · High vibration resistance up to 20 g 22 h/axis
- Polarized all-welded design
- · Self-healing behaviours
- Outstanding electrical performance

Part Number System



PHH223	М	LP	411	0	М	E4
Series Rated	Voltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Packaging
Hybrid Radial Crown Capacitor	J = 35 M = 63	See Dimension Table	The last two digits represent significant figures. The first digit indicates the total number digits.	0 = Standard	M = -20 +20%	E4 = Tray



Performance Characteristics

ltem		Performance Characteristics			
Capacitance Range	540 - 3,200 μF				
Rated Voltage	35 - 63 VDC				
Operating Temperature	-40 to +125°C				
Capacitance Tolerance	−20/+20%, at 100 Hz/+20°C				
Operational Lifetime	Rated Voltage and I _{RAC} at T _{case} 90°C/100kHz (hours)	Rated Voltage and I _{RAC} at T _{case} 105°C/100kHz	Rated Voltage and I _{RAC} at T _{case} 125°C/100kHz (hours)		
	≥ 3	≥ 2,000			
End of Life Requirement	Δ C/C < ±30%, ESR < 3 x initial ESR value, IL < initial specified limit				
Surge Voltage	1.15 x V _R				
High Temperature Storage	. .	000 hours at +125°C with no voltage ap C, capacitors shall meet the limits spec	5		
	I = 0.005 CV (μA)				
Leakage Current	C = rated capacitance (μ F), V = rated voltage (VDC). Voltage applied for 5 minutes at +20°C.				
	Proc	Requirements			
Vibration Test Specifications	1.5 mm displace 20 g maximum acceler for three 22-hour ses (capacitor cla	No leakage of electrolyte or other visible damage. Deviations in capacitance from initial measurements must not exceed: Δ C/C < 5%			
Standards	AEC-Q200; IEC 60384-4 long life grade 40/125/56				

Compensation Factor of Ripple Current (RC) vs. Frequency

Frequency	0.1 kHz	0.2 kHz	1 kHz	5 kHz	10 kHz	20 kHz	40 kHz	100 kHz
Coefficient	0.20	0.30	0.55	0.85	0.90	0.95	1	1

Test Method & Performance

Endurance Life Test						
Conditions	Performance					
Temperature	+125°C					
Test Duration	2,000 hours					
Voltage	The sum of DC voltage must not exceed the rated voltage of the capacitor					
Performance	The following specifications will be satisfied when the capacitor is tested at +20°C:					
Capacitance Change	Within 15% of initial value (within 10% at 1,000 hour test)					
Equivalent Series Resistance	≤ 1.5x specified limit (ESR measured at 100 kHz +20°C)					
Leakage Current	Does not exceed leakage current limit					



Ordering Options Table


Packaging Kind	Lead Length (mm)	Lead and Packaging Code				
Standard Packaging Option						
Tray	3.3 ±0.5	E4				

Dimensions – Millimeters

END VIEW (+)

SIDE VIEW





		Approximate				
Size Code	D	L	d	LL	Approximate Weight	
	±0.5	±1	±0.03	±0.5	Grams	
KL	16.2	27.7	1.0	3.3	9	
KP	16.2	35.7	1.0	3.3	11	
LL	18.2	27.7	1.0	3.3	11	
LP	18.2	35.7	1.0	3.3	16	



Shelf Life

The capacitance, ESR and impedance of a capacitor will not change significantly after extended storage periods at temperatures up to 40°C, however the leakage current will very slowly increase.

Environmental Compliance



All Part Numbers in this datasheet are Reach and RoHS compliant and Halogen-Free.

As an environmentally conscious company, KEMET is working continuously with improvements concerning the environmental effects of both our capacitors and their production.

In Europe (RoHS Directive) and in some other geographical areas such as China, legislation has been put in place to prevent the use of some hazardous materials, such as lead (Pb), in electronic equipment. All products in this catalog are produced to help our customers' obligations to guarantee their products and fulfill these legislative requirements. The only material of concern in our products has been lead (Pb), which has been removed from all designs to fulfill the requirement of containing less than 0.1% of lead in any homogeneous material. KEMET will closely follow any changes in legislation world wide and makes any necessary changes in its products, whenever needed.

Some customer segments such as medical, military, and automotive electronics may still require the use of lead in electrode coatings. To clarify the situation and distinguish products from each other, a special symbol is used on the packaging labels for RoHS compatible capacitors.

Due to customer requirements, there may appear additional markings such as LF = Lead-free or LFW = Lead-free wireson the label.



C _R	D x L	I _{RAC} ^a T _c = 90°C 100 kHz	I _{RAC} ^a T _c = 105°C 100 kHz	I _{RAC} ^b T _c = 125°C 100 kHz	ESR (Maximum) 20°C 100 Hz	ESR (Maximum) -40 to 125°C 100 kHz	Part Number		
μF	mm	A _{RMS}	A _{rms}	A _{rms}	mOhm	mOhm			
	35 VDC (U _s)								
1,400	16x27	39.0	34.0	23.4	112	4.7	PHH223JKL4140ME4		
2,100	16x35	39.8	34.7	23.9	80	4.5	PHH223JKP4210ME4		
2,200	18x27	44.8	39.0	26.9	78	3.9	PHH223JLL4220ME4		
3,200	18x35	46.0	40.1	27.6	48	3.7	PHH223JLP4320ME4		
	63 VDC (U _p)								
540	16x27	38	32.6	21.3	124	5.0	PHH223MKL3540ME4		
780	16x35	38.9	33.3	21.7	87	4.7	PHH223MKP3780ME4		
800	18x27	42.5	36.0	24.4	85	4.2	PHH223MLL3800ME4		
1,100	18x35	44.0	37.0	24.9	62	3.9	PHH223MLP4110ME4		


Table 1 – Ratings & Part Number Reference

^a 3,000 hours

^b 2,000 hours


Operational Life

Operational life ($L_{_{op}})$ at case temperature $T_{_c}$ and ripple current $I_{_{AC}}.$






Marking



Construction





Construction Data

The manufacturing process begins with the anode foil being electrochemically etched to increase the surface area and then "formed" to produce the aluminum oxide layer. Both the anode and cathode foils are then interleaved with absorbent paper and wound into a cylinder. During the winding process, aluminum tabs are attached to each foil to provide the electrical contact.

The winding is assembled to the capacitor Al-can and to the Al-lid. The can is filled with electrolyte and the winding is impregnated during a vacuum treatment. The capacitor is sealed. Throughout the process, all materials inside the housing must be maintained at the highest purity and be compatible with the electrolyte. Coating with polymer is applied during manufacturing process to achieve enhanced performance.

Each capacitor is aged and tested before being packed. The purpose of aging is to repair any damage in the oxide layer and thus reduce the leakage current to a very low level. Aging is carried out at elevated temperature and is accomplished by applying voltage to the device while carefully controlling the supply current. The process takes between 2 and 20 hours, depending on voltage rating.

Damage to the oxide layer can occur due to a variety of reasons:

- · Slitting of the anode foil after forming
- Attaching the tabs to the anode foil
- Minor mechanical damage caused during winding


The following tests are applied for each individual capacitor.


Electrical:

- Leakage current
- Capacitance
- ESR
- Tan Delta

Mechanical/Visual:

- · Pull strength test of wire terminals
- Print detail
- Box labels
- · Packaging, including packed quantity







KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

KEMET requires its products to be packaged and shipped on pallets. This is because KEMET's products are specifically designed to be packed onto pallets during shipment. If for any reason, the products are removed from pallets by the shipping party and shipped to the end customer, then additional external protection is required. In this instance, an external box with two carton layers and an upwards orientation sticker must be used by the shipping party, with the empty space filled with filling material, and afterwards sealing the box. If this packing and packaging guideline is not followed by the shipping party, the shipping party, and not KEMET, will be held responsible for any packaging, packing and/or product damages upon delivery of the products to the end customer. KEMET hereby disclaims any liability for damages to the products or otherwise that have been, or threaten to be, inflicted, result from or are in any way related to the packaging, packing or damage by the shipping party in contravention of the packaging guidelines herein.

KEMET is a registered trademark of KEMET Electronics Corporation.