



Click [here](#) for the 3D model.

Dimensions

| | |
|-------------|-----------------|
| D | 8mm +/-0.5mm |
| L | 12mm +/-1mm |
| S | 3.5mm +/-0.5mm |
| LL Negative | 15mm MIN |
| LL Positive | 19mm MIN |
| F | 0.6mm +/-0.05mm |

Packaging Specifications

| | |
|-----------|-----------|
| Packaging | Bulk, Bag |
|-----------|-----------|

General Information

| | |
|--------------|--------------------------------|
| Series | A759 |
| Dielectric | Polymer Aluminum |
| Description | Single Ended, Polymer Aluminum |
| RoHS | Yes |
| Lead | Wire Leads |
| AEC-Q200 | No |
| Halogen Free | Yes |

Specifications

| | |
|-----------------------|--|
| Capacitance | 100 uF |
| Capacitance Tolerance | 20% |
| Voltage DC | 35 VDC, 40.2 VDC (Surge) |
| Temperature Range | -55/+125°C |
| Rated Temperature | 125°C |
| Life | 2000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit) |
| Dissipation Factor | 12% 120Hz 20C |
| ESR | 31 mOhms (100kHz 20C) |
| Ripple Current | 4290 mAmps (100kHz 105C), 2500 mAmps (100kHz 125C) |
| Leakage Current | 525 uA (2min 20°C) |