



Click [here](#) for the 3D model.

### Dimensions

D	10mm +/-0.5mm
L	12mm +/-1mm
S	5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	19mm MIN
F	0.6mm +/-0.05mm

### Packaging Specifications

Packaging	Bulk, Bag
-----------	-----------

### General Information

Series	A759
Dielectric	Polymer Aluminum
Description	Single Ended, Polymer Aluminum
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Halogen Free	Yes

### Specifications

Capacitance	18 uF
Capacitance Tolerance	20%
Voltage DC	160 VDC, 184 VDC (Surge)
Temperature Range	-55/+125°C
Rated Temperature	125°C
Life	2000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit)
Dissipation Factor	12% 120Hz 20C
ESR	90 mOhms (100kHz 20C)
Ripple Current	1944 mAmps (100kHz 105C), 720 mAmps (100kHz 125C)
Leakage Current	432 uA (2min 20°C)