



Click [here](#) for the 3D model.

### Dimensions

D	18mm +/-0.5mm
L	31mm +/-2mm
S	7.5mm +/-0.5mm
F	0.8mm +/-0.05mm

### Packaging Specifications

Packaging	Bulk, Bag
-----------	-----------

### General Information

Series	A759
Dielectric	Polymer Aluminum
Description	Single Ended, Polymer Aluminum
RoHS	Yes
Lead	Cut
AEC-Q200	No
Halogen Free	Yes

### Specifications

Capacitance	82 uF
Capacitance Tolerance	20%
Voltage DC	250 VDC, 287.5 VDC (Surge)
Temperature Range	-55/+125°C
Rated Temperature	125°C
Life	2000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit)
Dissipation Factor	12% 120Hz 20C
ESR	150 mOhms (100kHz 20C)
Ripple Current	3200 mAmps (100kHz 105C), 1750 mAmps (100kHz 125C)
Leakage Current	3075 uA (2min 20°C)