


General Information

Series	A767
Dielectric	Polymer Aluminum
Style	SMD Can
Description	Surface Mount, Polymer Aluminum
RoHS	Yes
Lead	V-Chip
AEC-Q200	No
Halogen Free	Yes

[Click here](#) for the 3D model.

Dimensions

D	8mm +/-0.5mm	Capacitance	33 uF
L	9.7mm +/-0.3mm	Tolerance	20%
W	0.8 - 1.1mm	Voltage DC	35 VDC, 40.2 VDC (Surge)
F	0.2mm MAX	Temperature Range	-55/+105°C
A	8.3mm +/-0.2mm	Rated Temperature	105°C
B	8.3mm +/-0.2mm	Life	2000 Hrs
C	9mm +/-0.2mm	ESR	31 mOhms (100kHz 20C)
G	0.35mm +/-0.2mm	ESR	31 mOhms
P	3.1mm +/-0.2mm	Ripple Current	1900 mAmps (100kHz 105C)
		High Temperature Solder	Yes
		Leakage Current	300 uA (2min 20°C)

Packaging Specifications

Packaging	T&R, 380mm
Packaging Quantity	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.