



Click [here](#) for the 3D model.

General Information

Series	A780
Dielectric	Hybrid Polymer
Style	SMD Can
Description	Surface Mount, Polymer Aluminum
RoHS	Yes
Lead	V-Chip
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	true
Shelf Life	52 Weeks
MSL	1

Specifications

Capacitance	47 uF
Capacitance Tolerance	20%
Voltage DC	35 VDC, 40.25 VDC (Surge)
Temperature Range	-55/+125°C
Rated Temperature	125°C
Life	4000 Hrs
Dissipation Factor	12% 120Hz 20C
ESR	70 mOhms (100kHz 20C)
Ripple Current	880 mAmps (100kHz 125C)
Leakage Current	16.45 uA (2min 20°C)
High Temperature Solder	true

Dimensions

D	6.3mm +/-0.5mm
L	5.7mm +/-0.3mm
W	6.6mm +/-0.2mm
H	6.6mm +/-0.2mm
C	7.3mm +/-0.2mm
P	2mm NOM
R	0.5 - 0.8mm

Packaging Specifications

Packaging	T&R, 380mm
Packaging Quantity	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.