



Click [here](#) for the 3D model.

#### Dimensions

D	10mm +/-0.5mm
L	10.2mm +/-0.3mm
W	10.3mm +/-0.2mm
H	10.3mm +/-0.2mm
C	11mm +/-0.2mm
P	4.6mm NOM
R	0.8 - 1.1mm

#### Packaging Specifications

Packaging	T&R, 380mm
Packaging Quantity	500

#### General Information

Series	A780
Dielectric	Hybrid Polymer
Style	SMD Can
Description	Surface Mount, Polymer Aluminum
RoHS	Yes
Lead	V-Chip
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	true
Shelf Life	52 Weeks
MSL	1

#### Specifications

Capacitance	120 uF
Capacitance Tolerance	20%
Voltage DC	50 VDC, 57.5 VDC (Surge)
Temperature Range	-55/+125°C
Rated Temperature	125°C
Life	4000 Hrs
Dissipation Factor	10% 120Hz 20C
ESR	30 mOhms (100kHz 20C)
Ripple Current	1600 mAmps (100kHz 125C)
Leakage Current	60 uA (2min 20°C)
High Temperature Solder	true