
## A785KS337M1ELAS027

A785, Aluminum, Hybrid Polymer, 330 uF, 20%, 25 VDC, -55/+150°C





Click here for the	he 3D model.
--------------------	--------------

General Information	
Series	A785
Dielectric	Hybrid Polymer
Style	SMD Can
Description	Surface Mount, Hybrid Aluminum Polymer
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	Yes
Shelf Life	52 Weeks
MSL	1

Dimensions	
D	8mm +/-0.5mm
L	12.2mm +/-0.3mm
W	8.3mm +/-0.2mm
Н	8.3mm +/-0.2mm
С	9mm +/-0.2mm
Р	3.1mm NOM
R	0.8 - 1.1mm

Packaging Specifications	
Packaging	T&R, 380mm
Packaging Quantity	400

Specifications	
Capacitance	330 uF
Tolerance	20%
Voltage DC	25 VDC, 28.75 VDC (Surge)
Temperature Range	-55/+150°C
Rated Temperature	150°C
Life	1000 Hrs
Dissipation Factor	14% 120Hz 20C
ESR	27 mOhms (100kHz 20C)
Ripple Current	2800 mAmps (100kHz 125C), 1800 mAmps (100kHz 135C), 900 mAmps (100kHz 150C)
High Temperature Solder	Yes
Leakage Current	82.5 uA (2min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/22/2025 © 2006 - 2025 YAGEO