



Click [here](#) for the 3D model.

General Information

Series	A785
Dielectric	Hybrid Polymer
Style	SMD Can
Description	Surface Mount, Polymer Aluminum
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	Yes
Shelf Life	52 Weeks
MSL	1

Dimensions

D	10mm +/-0.5mm
L	16.5mm +/-0.5mm
W	10.3mm +/-0.2mm
H	10.3mm +/-0.2mm
C	11mm +/-0.2mm
P	4.6mm NOM
R	0.8 - 1.1mm

Packaging Specifications

Packaging	T&R, 380mm
Packaging Quantity	250

Specifications

Capacitance	470 uF
Tolerance	20%
Voltage DC	35 VDC, 40.25 VDC (Surge)
Temperature Range	-55/+150°C
Rated Temperature	150°C
Life	1000 Hrs
Dissipation Factor	12% 120Hz 20C
ESR	15 mOhms (100kHz 20C)
Ripple Current	4300 mAmps (100kHz 125C), 2600 mAmps (100kHz 135C), 1800 mAmps (100kHz 150C)
High Temperature Solder	Yes
Leakage Current	164.5 uA (2min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.