
A785KN476M1JLAS045

A785, Aluminum, Hybrid Polymer, 47 uF, 20%, 63 VDC, -55/+150°C





Click	horo	for	tha	3D	model

General Information	
Series	A785
Dielectric	Hybrid Polymer
Style	SMD Can
Description	Surface Mount, Hybrid Aluminum Polymer
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	Yes
Shelf Life	52 Weeks
MSL	1

Dimensions	
D	8mm +/-0.5mm
L	9.7mm +/-0.3mm
W	8.3mm +/-0.2mm
Н	8.3mm +/-0.2mm
С	9mm +/-0.2mm
P	3.1mm NOM
R	0.8 - 1.1mm

Packaging Specifications		
Packaging	T&R, 380mm	
Packaging Quantity	500	

Specifications	
Capacitance	47 uF
Tolerance	20%
Voltage DC	63 VDC, 72.45 VDC (Surge)
Temperature Range	-55/+150°C
Rated Temperature	150°C
Life	1000 Hrs
Dissipation Factor	8% 120Hz 20C
ESR	45 mOhms (100kHz 20C)
Ripple Current	2400 mAmps (100kHz 125C), 1700 mAmps (100kHz 135C), 1100 mAmps (100kHz 150C)
High Temperature Solder	Yes
Leakage Current	29.6 uA (2min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/06/2025 © 2006 - 2025 YAGEO