



Click [here](#) for the 3D model.

Dimensions

D	8mm +/-0.5mm
L	12.2mm +/-0.3mm
W	8.3mm +/-0.2mm
H	8.3mm +/-0.2mm
C	9mm +/-0.2mm
P	3.1mm NOM
R	0.8 - 1.1mm

Packaging Specifications

Packaging	T&R, 380mm
Packaging Quantity	400

General Information

Series	A785
Dielectric	Hybrid Polymer
Style	SMD Can
Description	Surface Mount, Polymer Aluminum
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	true
Shelf Life	52 Weeks
MSL	1

Specifications

Capacitance	68 uF
Capacitance Tolerance	20%
Voltage DC	63 VDC, 72.45 VDC (Surge)
Temperature Range	-55/+150°C
Rated Temperature	150°C
Life	1000 Hrs
Dissipation Factor	8% 120Hz 20C
ESR	40 mOhms (100kHz 20C)
Ripple Current	2700 mAmps (100kHz 125C), 1900 mAmps (100kHz 135C), 1200 mAmps (100kHz 150C)
Leakage Current	42.8 uA (2min 20°C)
High Temperature Solder	true