




Click [here](#) for the 3D model.

General Information

Style	Resin Coated
Description	Resin Coated Type Multilayer Piezoelectric Actuators
RoHS	With Exemptions
REACH	SVHC (PZT – CAS 12626-81-2)

Dimensions

W	5mm +/-0.1mm
W2	6.5mm MAX
H	20mm +/-0.1mm
T	5mm +/-0.1mm
T2	6.5mm MAX

Packaging Specifications

Typical Component Weight	5
Packaging	Bulk
Packaging Quantity	10

Specifications

Series	AL
Displacement	17um +/-2um
Voltage DC	150 VDC
Capacitance	1.1 uF
Tolerance	20%
Resonant Frequency	70 kHz
Tensile Strength	85 N
Young's Modulus	5.2x10 ¹⁰ N/m ²
Generated Force	850 N
Stiffness	50 N/um
Insulation Resistance	50 MOhms
Temperature Range	-25/+150°C

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.