



Click [here](#) for the 3D model.

#### Dimensions

D	30mm +1mm
L	40mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	160

#### General Information

Series	ALA7D
Dielectric	Aluminum Electrolytic
Style	Snap-In
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
Qualifications	AEC-Q200
AEC-Q200	Yes
Halogen Free	true
Typical Component Weight	50 g
Miscellaneous	Vibration: <= 35mm 1.5mm displacement amplitude or 20G maximum acceleration. Vibration applied for three directions of 4-hour sessions at 10-2,000 Hz. (Capacitor clamped by body.)
Shelf Life	156 Weeks

#### Specifications

Capacitance	160 uF
Capacitance Tolerance	20%
Voltage DC	600 VDC, 660 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	13000 Hrs (Rated Voltage And Ripple Current At 85C), 21000 Hrs (Rated Voltage at 85C)
ESR	797 mOhms (100Hz 20C), 550 mOhms (10kHz 20C)
Ripple Current	1.6 Amps (100Hz 85C), 3.5 Amps (10kHz 85C)
Leakage Current	576 uA (5min 20°C)