



Click [here](#) for the 3D model.

### Dimensions

W	5mm +/-0.1mm
W2	5.4mm MAX
H	10mm +/-0.1mm
T	5mm +/-0.1mm
T2	5.4mm MAX
LL	100mm +/-5mm

### Packaging Specifications

Typical Component Weight	1.56
Packaging	Bulk
Packaging Quantity	4

### General Information

Style	Resin Coated
Description	Resin Coated Type Multilayer Piezoelectric Actuators
Young's Modulus	4.4x10 <sup>10</sup> N/m <sup>2</sup>
RoHS	Yes
REACH	Yes

### Specifications

Series	AE
Displacement	9.1um +/-1.5um
Voltage DC	150 VDC
Capacitance	0.54 uF
Capacitance Tolerance	20%
Resonant Frequency	138 kHz
Tensile Strength	61 N
Generated Force	610 N
Stiffness	67 N/um
Insulation Resistance	10 MOhms
Temperature Range	-25/+85°C