



Click [here](#) for the 3D model.

### Dimensions

D	30mm +1mm
L	40mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

### Packaging Specifications

Packaging	Tray
-----------	------

### General Information

Series	ALC40
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
AEC-Q200	No
Typical Component Weight	45 g
Shelf Life	156 Weeks

### Specifications

Capacitance	5,600 uF
Capacitance Tolerance	20%
Voltage DC	63 VDC, 72.45 VDC (Surge)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	7000 Hrs (Rated Voltage And Ripple Current At 105C), 11000 Hrs (Rated Voltage At 105C)
ESR	122 mOhms (100Hz 20C), 102 mOhms (10kHz 20C)
Ripple Current	2.61 Amps (100Hz 105C), 3.03 Amps (10kHz 105C)
Leakage Current	1058 uA (5min 20°C)