



Click [here](#) for the 3D model.

Dimensions

| | |
|----|---------------|
| D | 35mm NOM |
| L | 80mm NOM |
| S | 10mm +/-0.1mm |
| LL | 6.3mm +/-1mm |
| F | 2mm +/-0.1mm |

Packaging Specifications

| | |
|-----------|------|
| Sleeving | Yes |
| Packaging | Tray |

General Information

| | |
|--------------------------|------------------------------|
| Series | ALC10S |
| Dielectric | Aluminum Electrolytic |
| Description | Audio Grade Snap-In |
| Features | Audio Grade |
| RoHS | Yes |
| Lead | 2 Pin |
| AEC-Q200 | No |
| Typical Component Weight | 105 g |
| Notes | Dimensions Include Sleeving. |
| Shelf Life | 156 Weeks |

Specifications

| | |
|-------------------|---------------------|
| Capacitance | 10,000 uF |
| Tolerance | 20% |
| Voltage DC | 80 VDC |
| Temperature Range | -40/+85°C |
| Rated Temperature | 85°C |
| Life | 15000 Hrs |
| Leakage Current | 4800 uA (5min 20°C) |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.