


 Click [here](#) for the 3D model.

**General Information**

Series	ALC80
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin Short
Halogen Free	Yes
Typical Component Weight	28 g
Notes	Dimensions D And L Include Sleeving.
Shelf Life	156 Weeks

**Dimensions**

D	25mm +1mm
L	30mm +/-2mm
S	10mm +/-0.1mm
LL	4mm +/-1mm
F	2mm +/-0.1mm

**Packaging Specifications**

Sleeving	Yes
Packaging	Bulk, Bag

**Specifications**

Capacitance	110 uF
Tolerance	20%
Voltage DC	400 VDC, 440 VDC (Surge)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	6000 Hrs (Rated Voltage And Ripple Current At 105C), 10000 Hrs (Rated Voltage at 105C)
ESR	1106 mOhms (100Hz 20C), 566.7 mOhms (10kHz 20C)
Ripple Current	0.912 Amps (100Hz 105C), 2.615 Amps (10kHz 105C)
Leakage Current	132 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.