



Click [here](#) for the 3D model.

General Information

Series	ALH82
Dielectric	Aluminum Electrolytic
Style	Snap-In
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
AEC-Q200	No
Halogen Free	true
Typical Component Weight	115 g
Shelf Life	156 Weeks

Dimensions

D	35mm +/-1mm
L	80mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications

Packaging	Tray
-----------	------

Specifications

Capacitance	390 uF
Capacitance Tolerance	20%
Voltage DC	600 VDC
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	3000 Hrs (Rated Voltage And Ripple Current At 105C)
ESR	362 mOhms (100Hz 20C), 245 mOhms (10kHz 20C)
Ripple Current	2.95 Amps (100Hz 105C), 7.61 Amps (10Hz 105C)
Leakage Current	702 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.