



Click [here](#) for the 3D model.

### Dimensions

D	35mm +/-1mm
L	80mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

### Packaging Specifications

Packaging	Tray
-----------	------

### General Information

Series	ALH82
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
AEC-Q200	No
Halogen Free	Yes
Typical Component Weight	115 g
Shelf Life	156 Weeks

### Specifications

Capacitance	390 uF
Capacitance Tolerance	20%
Voltage DC	600 VDC
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	3000 Hrs (Rated Voltage And Ripple Current At 105C)
ESR	362 mOhms (100Hz 20C), 245 mOhms (10kHz 20C)
Ripple Current	2.95 Amps (100Hz 105C), 7.61 Amps (10Hz 105C)
Leakage Current	702 uA (5min 20°C)