



Click [here](#) for the 3D model.

Dimensions

D	30mm +/-1mm
L	30mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications

Packaging	Tray
-----------	------

General Information

Series	ALH82
Dielectric	Aluminum Electrolytic
Style	Snap-In
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
AEC-Q200	No
Halogen Free	true
Typical Component Weight	40 g
Shelf Life	156 Weeks

Specifications

Capacitance	75 uF
Capacitance Tolerance	20%
Voltage DC	600 VDC
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	3000 Hrs (Rated Voltage And Ripple Current At 105C)
ESR	1861 mOhms (100Hz 20C), 1257 mOhms (10kHz 20C)
Ripple Current	0.97 Amps (100Hz 105C), 2.74 Amps (10Hz 105C)
Leakage Current	135 uA (5min 20°C)