



Click [here](#) for the 3D model.

**General Information**

Series	ALS36
Dielectric	Aluminum Electrolytic
Style	Screw Terminal
Description	Screw Terminal, Aluminum Electrolytic
RoHS	Yes
Lead	Oval Threaded Inserts M5
Mounting	Through-Hole
AEC-Q200	No
Typical Component Weight	700 g
Notes	Add 0.015 in/ 0.4 mm to D and 0.045 in/ 1.1 mm to L for Sleeving. MS (MxH) = M12x16. Mounting Clamp (Sold Separately): V11
Shelf Life	156 Weeks

**Dimensions**

D	76.2mm +/-0.787mm
L	104.775mm +/-1.575mm
T	5.512mm +/-0.787mm
S	31.75mm +/-0.483mm
DT	8.001mm +/-0.483mm
LT	111.506mm +/-0.991mm
TD	10.008mm MIN
V	18.999mm NOM
Z	10.008mm NOM

**Packaging Specifications**

Packaging	Bulk, Box
-----------	-----------

**Specifications**

Capacitance	68000 uF
Capacitance Tolerance	-10/+30%
Voltage DC	63 VDC, 67 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	20000 Hrs (Rated Voltage And Ripple Current At 85C), 40000 Hrs (Rated Voltage at 85C)
ESR	8 mOhms (120Hz 25C), 7 mOhms (20kHz 25C)
Ripple Current	26.4 Amps (120Hz 85C), 28 Amps (20kHz 85C)
Leakage Current	6000 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.