



Click [here](#) for the 3D model.

Dimensions	
D	66mm +/-1mm
L	82mm +/-2mm
T	5.5mm +/-0.5mm
S	28.5mm +/-0.5mm
DT	13mm +/-0.5mm
LT	86mm +/-1mm
TD	10mm MIN
V	15.8mm NOM
Z	10mm NOM

Packaging Specifications	
Sleeving	true
Packaging	Bulk, Box

General Information	
Series	ALS60
Dielectric	Aluminum Electrolytic
Style	Screw Terminal
Description	High Voltage, Screw Terminal, Aluminum Electrolytic
RoHS	Yes
Lead	Screw Terminals M6
Mounting	Through-Hole
AEC-Q200	No
Typical Component Weight	428 g
Notes	Dimensions D And L Include Sleeving. MS (MxH) = M12x16.

Specifications	
Capacitance	1000 uF
Capacitance Tolerance	20%
Voltage DC	550 VDC, 605 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	19000 Hrs
ESR	303.3 mOhms (100Hz 20C), 268.8 mOhms (10kHz 20C)
Ripple Current	6.51 Amps (100Hz 85C), 10.55 Amps (10kHz 85C)
Leakage Current	3300 uA (5min 20°C)