



Click [here](#) for the 3D model.

General Information	
Series	ALS60
Dielectric	Aluminum Electrolytic
Description	High Voltage, Screw Terminal, Aluminum Electrolytic
RoHS	Yes
Lead	Screw Terminals M6
Mounting	Through-Hole
AEC-Q200	No
Typical Component Weight	540 g
Notes	Dimensions D And L Include Sleeving. MS (MxH) = M12x16.

Specifications	
Capacitance	1,500 μ F
Tolerance	20%
Voltage DC	550 VDC, 605 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	19000 Hrs
ESR	203.9 mOhms (100Hz 20C), 180.6 mOhms (10kHz 20C)
Ripple Current	8.97 Amps (100Hz 85C), 14.08 Amps (10kHz 85C)
Leakage Current	4950 μ A (5min 20°C)

operating conditions for such applications, but are not intended to constitute - and are not to be used for - any application or use. This Information is intended for use only by customers who have the necessary technical knowledge and experience. Any technical advice inferred from this Information or otherwise provided by us is not intended to constitute, and is not to be used for, any application or use.

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.