



Click [here](#) for the 3D model.

**Dimensions**

D	35mm +/-1mm
L	35mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

**Packaging Specifications**

Packaging	Tray
-----------	------

**General Information**

Series	ALH82
Dielectric	Aluminum Electrolytic
Style	Snap-In
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
AEC-Q200	No
Halogen Free	true
Typical Component Weight	60 g
Shelf Life	156 Weeks

**Specifications**

Capacitance	130 uF
Capacitance Tolerance	20%
Voltage DC	600 VDC
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	3000 Hrs (Rated Voltage And Ripple Current At 105C)
ESR	1079 mOhms (100Hz 20C), 730 mOhms (10kHz 20C)
Ripple Current	1.45 Amps (100Hz 105C), 3.96 Amps (10Hz 105C)
Leakage Current	234 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.