



General Information	
Series	ALS36
Dielectric	Aluminum Electrolytic
Style	Screw Terminal
Description	Screw Terminal, Aluminum Electrolytic
RoHS	Yes
Lead	Screw Terminals M6
Mounting	Through-Hole
AEC-Q200	No
Typical Component Weight	661 g
Notes	Add 0.015 in/ 0.4 mm to D and 0.045 in/ 1.1 mm to L for Sleeving. Dimension LT Available On Request. MS (MxH) = M12x16. Mounting Clamp (Sold Separately): V8
Shelf Life	156 Weeks

Click [here](#) for the 3D model.

Dimensions	
D	63.5mm +/-0.787mm
L	142.875mm +/-1.575mm
T	6.35mm +/-0.787mm
S	28.575mm +/-0.483mm
DT	17.018mm +/-0.483mm
TD	11.811mm MIN
V	15.799mm NOM

Packaging Specifications	
Packaging	Bulk, Box

Specifications	
Capacitance	220000 uF
Capacitance Tolerance	-10/+30%
Voltage DC	25 VDC, 30 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	19000 Hrs (Rated Voltage And Ripple Current At 85C), 38000 Hrs (Rated Voltage At 85C)
ESR	6 mOhms (120Hz 25C), 6 mOhms (20kHz 25C)
Ripple Current	31.4 Amps (120Hz 85C), 32.8 Amps (20kHz 85C)
Leakage Current	6000 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.