


General Information

| | |
|--------------------------|--------------------------------------|
| Series | ALT20 |
| Dielectric | Aluminum Electrolytic |
| Description | Solder Tag, Aluminum Electrolytic |
| RoHS | Yes |
| Lead | 2 Flying Leads Solder Tags |
| Typical Component Weight | 50 g |
| Notes | Dimensions D And L Include Sleeving. |
| Shelf Life | 156 Weeks |

[Click here](#) for the 3D model.

Dimensions

| | |
|----|---------------|
| D | 30mm +/-1mm |
| L | 45mm +/-2mm |
| S | 10mm +/-0.1mm |
| LL | 10mm +/-0.5mm |

Specifications

| | |
|-------------------|------------------------|
| Capacitance | 3,300 uF |
| Tolerance | -10/+30% |
| Voltage DC | 40 VDC, 46 VDC (Surge) |
| Temperature Range | -40/+85°C |
| Rated Temperature | 85°C |
| Life | 15000 Hrs |
| Leakage Current | 792 uA (5min 20°C) |

Packaging Specifications

| | |
|-----------|------|
| Sleeving | Yes |
| Packaging | Tray |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.