


[Click here for the 3D model.](#)
General Information

Series	ALT22
Dielectric	Aluminum Electrolytic
Description	Solder Tag, Aluminum Electrolytic
RoHS	Yes
Lead	2 Flying Leads Solder Tags
AEC-Q200	No
Typical Component Weight	170 g
Notes	Dimensions D And L Include Sleevng.

Dimensions

D	40mm +/-1mm
L	105mm +/-2mm
S	10mm +/-0.1mm
LL	10mm +/-0.5mm

Specifications

Capacitance	10,000 uF
Tolerance	20%
Voltage DC	100 VDC, 115 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	26000 Hrs
Leakage Current	6000 uA (5min 20°C)

Packaging Specifications

Sleevng	Yes
Packaging	Tray

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.