


ALS61A222MP550

Not for New Design

General Information

ALS61, Aluminum, Aluminum Electrolytic, 2,200 uF, 20%, 550 VDC, -40/ $+85^{\circ}$ C, 28.5 mm



Series	ALS61
Dielectric	Aluminum Electrolytic
Description	High Voltage, Screw Terminal, Aluminum Electrolytic
RoHS	Yes
Lead	Oval Threaded Inserts M5
Mounting	Through-Hole
Optional Mounting	Stud
AEC-Q200	No
Typical Component Weight	675 g
Notes	Dimensions D And L Include Sleeving. MS (MxH) = M12x16.

Click here for the 3D model.

Dimensions	
D	66mm +/-1mm
L	146mm +/-2mm
T	5.5mm +/-0.5mm
S	28.5mm +/-0.5mm
DT	13mm +/-0.5mm
LT	150mm +/-1mm
TD	10mm MIN
V	15.8mm NOM
Z	10mm NOM

Packaging Specifications	
Sleeving	Yes
Packaging	Bulk, Box

Specifications	
Capacitance	2,200 uF
Tolerance	20%
Voltage DC	550 VDC, 605 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	19000 Hrs
ESR	140.3 mOhms (100Hz 20C), 124.4 mOhms (10kHz 20C)
Ripple Current	11.25 Amps (100Hz 85C), 17.1 Amps (10kHz 85C)
Leakage Current	6000 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/28/2025 © 2006 - 2025 YAGEO