




ALS80, Aluminum, Aluminum Electrolytic, 5,600 uF, 20%, 100 VDC, –40/ +105°C, 12.8 mm



Click	here	for	the	3D	model.
-------	------	-----	-----	----	--------

General Information	
Series	ALS80
Dielectric	Aluminum Electrolytic
Description	Screw Terminal, Aluminum Electrolytic
RoHS	Yes
Lead	ThreadedInserts - 10-32 UNF class 2B
Mounting	Through-Hole
AEC-Q200	No
Halogen Free	Yes
Typical Component Weight	115 g
Notes	Dimensions D And L Include Sleeving. MS (MxH) = M8x12. Mounting Clamp (Sold Separately): V3/H2/2736
Shelf Life	156 Weeks

Dimensions		
D	36mm +/-1mm	
L	82mm +/-2mm	
Т	7.1mm +/-0.5mm	
S	12.8mm +/-0.5mm	
DT	8mm +/-0.5mm	
LT	Available On Request	
TD	10mm MIN	
V	8mm NOM	
Packaging Specifications		

Packaging Specifications	
Sleeving	Yes
Packaging	Tray

Specifications	
Capacitance	5,600 uF
Tolerance	20%
Voltage DC	100 VDC, 115 VDC (Surge)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	6000 Hrs (Rated Voltage And Ripple Current At 105C), 10000 Hrs (Rated Voltage at 105C)
ESR	53 mOhms (100Hz 20C), 43 mOhms (10kHz 20C)
Ripple Current	8.5 Amps (100Hz 105C), 12.3 Amps (10 kHz 105C)
Leakage Current	1680 uA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/22/2025 © 2006 - 2025 YAGEO