



Click [here](#) for the 3D model.

General Information

Style	Metal Sealed
Description	Metal Sealed Type Multilayer Piezoelectric Actuators
RoHS	With Exemptions
SCIP Number	e8b63861-aef3-4ef5-83bb-6273ea2dbdde
Notes	Female thread type, V Groove.
REACH	SVHC (PZT - CAS 12626-81-2)

Specifications

Series	ASL
Displacement	19um +/-3um
Voltage DC	150 VDC
Capacitance	1.3 uF
Tolerance	20%
Resonant Frequency	14 kHz
Generated Force	800 N
Insulation Resistance	30 MOhms
Temperature Range	-40/+150°C

Dimensions

D	19.6mm +/-0.5mm
L	38.4mm +/-0.5mm
LL	130mm +/-10mm

Packaging Specifications

Typical Component Weight	46
Packaging	Tray
Packaging Quantity	1