



Click [here](#) for the 3D model.

**General Information**

|                         |  |
|-------------------------|--|
| Series                  | LDD Mil X7R C11015   |
| Style                   | Radial   |
| RoHS                    | No   |
| Prop 65                 | <b>⚠ WARNING:</b> Cancer and reproductive harm - <a href="http://www.p65warnings.ca.gov">http://www.p65warnings.ca.gov</a> . |
| Termination             | Lead (SnPb)  |
| Lead                    | Hockey Stick   |
| Failure Rate            | N/A  |
| Testing and Reliability | MIL-PRF-11015  |
| Qualifications          | MIL-PRF-11015  |
| AEC-Q200                | No   |
| Notes                   | Lead Length Shown Is For Parts Supplied In Bulk, See Packaging Specifications For Lead Lengths When Not Provided In Bulk.    |

**Specifications**

|                                 |            |
|---------------------------------|------------|
| Capacitance                     | 33 pF      |
| Capacitance Tolerance           | 20%        |
| Voltage DC                      | 200 VDC    |
| Dielectric Withstanding Voltage | 500 VDC    |
| Temperature Range               | -55/+125°C |
| Temperature Coefficient         | BX         |
| Dissipation Factor              | 2.5%       |
| Insulation Resistance           | 100 GOhms  |

**Dimensions**

|    |                         |
|----|-------------------------|
| L  | 4.83mm +/-0.25mm        |
| H  | 4.83mm +/-0.25mm        |
| T  | 2.29mm +/-0.25mm        |
| S  | 5.08mm +/-0.38mm        |
| LL | 31.75mm MIN             |
| F  | 0.635mm +0.102/-0.051mm |
| G  | 1.143mm MAX             |
| K  | 4.826mm +/-0.254mm      |

**Packaging Specifications**

|                    |                         |
|--------------------|-------------------------|
| Packaging          | Ammo, Type I, HO = 16mm |
| Packaging Quantity | 2000                    |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.