




Click [here](#) for the 3D model.

| General Information      |                                                                                                                              |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Series                   | SMD COTS X7R                                                                                                                 |
| Style                    | SMD Chip                                                                                                                     |
| Description              | SMD, MLCC, COTS, Temperature Stable, Class II                                                                                |
| Features                 | Temperature Stable, Class II                                                                                                 |
| RoHS                     | No                                                                                                                           |
| Prop 65                  | <b>⚠ WARNING:</b> Cancer and reproductive harm - <a href="http://www.p65warnings.ca.gov">http://www.p65warnings.ca.gov</a> . |
| Termination              | Lead (SnPb)                                                                                                                  |
| Marking                  | false                                                                                                                        |
| Failure Rate             | Testing per MIL-PRF-55681 PDA 8%, DPA per EIA-469                                                                            |
| AEC-Q200                 | No                                                                                                                           |
| Typical Component Weight | 4.8 mg                                                                                                                       |
| Shelf Life               | 78 Weeks                                                                                                                     |
| MSL                      | 1                                                                                                                            |

| Specifications                                                     |                                                 |
|--------------------------------------------------------------------|-------------------------------------------------|
| Capacitance                                                        | 0.1 uF                                          |
| Measurement Condition                                              | 1 kHz 1.0Vrms                                   |
| Capacitance Tolerance                                              | 5%                                              |
| Voltage DC                                                         | 16 VDC                                          |
| Dielectric Withstanding Voltage                                    | 40 VDC                                          |
| Temperature Range                                                  | -55/+125°C                                      |
| Temperature Coefficient                                            | X7R                                             |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 15%, 1kHz 1.0Vrms                               |
| Dissipation Factor                                                 | 3.5% 1 kHz 1.0Vrms                              |
| Aging Rate                                                         | 3% Loss/Decade Hour: Referee Time is 1000 Hours |
| Insulation Resistance                                              | 5 GOhms                                         |

| Dimensions |                  |
|------------|------------------|
| Chip Size  | 0603             |
| L          | 1.6mm +/-0.15mm  |
| W          | 0.8mm +/-0.15mm  |
| T          | 0.8mm +/-0.07mm  |
| S          | 0.7mm MIN        |
| B          | 0.35mm +/-0.15mm |

| Packaging Specifications |                                   |
|--------------------------|-----------------------------------|
| Packaging                | T&R, 330mm, 2mm Pitch, Paper Tape |
| Packaging Quantity       | 30000                             |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.