


M3253505E1C102JZMB-T&R

Aliases (C1206K102J2EML7189) SMD MIL COG PRF32535, Ceramic, 1,000 pF, 5%, 200 VDC, COG, SMD, Low ESR, MIL-PRF-32535, N/A, 1206 / 3216



General Information	
Series	SMD MIL COG PRF32535
Style	SMD Chip
Description	SMD, Low ESR, MIL-PRF-32535
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov /
SCIP Number	d66873f5-e54d-410c-a0cf-ebf6 fcf635b5
Termination	Solder Plated
Failure Rate	N/A
Qualifications	MIL-PRF-32535 M-Level
AEC-Q200	No
Shelf Life	78 Weeks
MSL	1

Dimensions	
L	3.2mm +0.3/-0.25mm
W	1.6mm +0.3/-0.25mm
Т	1.8mm MAX
В	0.51mm +/-0.36mm
Case Code (EIA / mm)	1206 / 3216

Packaging Specifications	
Packaging	T&R
Packaging Quantity	4000

Specifications	
Capacitance	1,000 pF
Tolerance	5%
Voltage DC	200 VDC
Dielectric Withstanding Voltage	500 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	COG
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	30 ppm/C, 1MHz 1.0Vrms
Dissipation Factor	0.15% 1 MHz 1.0Vrms
Aging Rate	0% Loss/Decade Hour
Insulation Resistance	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 11/05/2025 © 2006 - 2025 YAGEO