


CDR32BX103BKUR-T&R

Aliases (C1206N103K1XRL7189, CDR32BX103BKZR-T&R, CDR32BX103BKWR-T&R)

SMD Mil PRF55681, Ceramic, 0.01 uF, 10%, 100 VDC, BX, Ceramic Chips, MIL PRF 55681 Established Reliability, R (0.01%/1000 Hrs), 1206 / 3216



General Information	
Series	SMD Mil PRF55681
Style	SMD Chip
Description	Ceramic Chips, MIL PRF 55681 Established Reliability
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov /
SCIP Number	db44bada-287e-465e-9a06-2b9 3bb6487ea
Termination	Lead (SnPb)
Failure Rate	R (0.01%/1000 Hrs)
Testing and Reliability	MIL-PRF-55681
Qualifications	MIL-PRF-55681
AEC-Q200	No
Shelf Life	78 Weeks
MSL	1

Dimensions	
L	3.2mm +/-0.20mm
W	1.6mm +/-0.2mm
Т	1.3mm MAX
В	0.5mm +/-0.20mm
Case Code (EIA / mm)	1206 / 3216
Packaging Specifications	

2500

Packaging

Packaging Quantity

T&R, 178mm, Plastic Tape

Specifications	
Capacitance	0.01 uF
Tolerance	10%
Voltage DC	100 VDC
Dielectric Withstanding Voltage	250 VDC
Temperature Range	-55/+125°C
Temp. Coefficient	BX
Dissipation Factor	2.5%
Insulation Resistance	100 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute -	and
we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have	the د
requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by	y us
with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.	•

Generated 12/06/2025 © 2006 - 2025 YAGEO