

## C1210X274KARACTU

Aliases (C1210X274KARAC7800)

SMD Comm X7R Flex, Ceramic, 0.27 uF, 10%, 250 VDC, X7R, SMD, MLCC, FT-CAP, Temperature Stable, 1210



Click [here](#) for the 3D model.

| General Information      |                                       |
|--------------------------|---------------------------------------|
| Series                   | SMD Comm X7R Flex                     |
| Style                    | SMD Chip                              |
| Description              | SMD, MLCC, FT-CAP, Temperature Stable |
| Features                 | FT-CAP, Temperature Stable            |
| RoHS                     | Yes                                   |
| Termination              | Flexible Termination                  |
| Marking                  | false                                 |
| AEC-Q200                 | No                                    |
| Typical Component Weight | 85 mg                                 |
| Shelf Life               | 78 Weeks                              |
| MSL                      | 1                                     |

| Specifications   |   |
|--|---|
| Capacitance  | 0.27 uF   |
| Measurement Condition  | 1 kHz 1.0Vrms                                   |
| Capacitance Tolerance  | 10%   |
| Voltage DC   | 250 VDC   |
| Dielectric Withstanding Voltage                                    | 625 VDC   |
| Temperature Range  | -55/+125°C                                      |
| Temperature Coefficient  | X7R   |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 15%, 1kHz 1.0Vrms                               |
| Dissipation Factor   | 2.5% 1kHz 1.0Vrms                               |
| Aging Rate   | 3% Loss/Decade Hour: Referee Time is 1000 Hours |
| Insulation Resistance  | 370.4 MOhms                                     |

| Dimensions |                 |
|------------|-----------------|
| Chip Size  | 1210            |
| L          | 3.3mm +/-0.4mm  |
| W          | 2.6mm +/-0.3mm  |
| T          | 1.6mm +/-0.20mm |
| S          | 1.5mm MIN       |
| B          | 0.6mm +/-0.25mm |

| Packaging Specifications |                          |
|--------------------------|--------------------------|
| Packaging                | T&R, 180mm, Plastic Tape |
| Packaging Quantity       | 2000                     |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.