



Click [here](#) for the 3D model.

Dimensions

L	4.5mm +/-0.3mm
W	3.2mm +/-0.3mm
T	3.5mm +/-0.4mm
B	0.6mm +/-0.35mm

Packaging Specifications

Packaging	T&R, 180mm, Plastic Tape
Packaging Quantity	500

General Information

Series	KONNEKT Comm U2J
Style	KONNEKT
Description	SMD, MLCC, KONNEKT, Ultra-Stable, Class I
Features	High Density Packaging
RoHS	Yes
Termination	Tin
AEC-Q200	No
Chip Size	1812-2
Shelf Life	78 Weeks
MSL	1

Specifications

Capacitance	0.94 uF
Capacitance Tolerance	5%
Voltage DC	50 VDC
Dielectric Withstanding Voltage	125 VDC
Temperature Range	-55/+125°C
Temperature Coefficient	U2J
Dissipation Factor	0.1% 1 kHz 25C
Aging Rate	0.1% Loss/Decade Hour
Insulation Resistance	1.0638 GOhms