



Click [here](#) for the 3D model.

**General Information**

|                          |   |
|--------------------------|---|
| Series                   | SMD Auto X7R HV   |
| Style                    | SMD Chip  |
| Description              | SMD, MLCC, High Voltage, Temperature Stable, Automotive Grade |
| Features                 | High Voltage, Temp Stable, Automotive Grade                   |
| RoHS                     | Yes   |
| Termination              | Tin   |
| Marking                  | false   |
| Qualifications           | AEC-Q200  |
| AEC-Q200                 | Yes   |
| Typical Component Weight | 230 mg  |
| Shelf Life               | 78 Weeks  |
| MSL                      | 1   |

**Dimensions**

|           |                 |
|-----------|-----------------|
| Chip Size | 2220            |
| L         | 5.7mm +/-0.4mm  |
| W         | 5mm +/-0.4mm    |
| T         | 1.6mm +/-0.20mm |
| S         | 3.5mm MIN       |
| B         | 0.6mm +/-0.35mm |

**Packaging Specifications**

|                    |                          |
|--------------------|--------------------------|
| Packaging          | T&R, 180mm, Plastic Tape |
| Packaging Quantity | 1000                     |

**Specifications**

|  |   |
|--|---|
| Capacitance  | 2700 pF   |
| Measurement Condition  | 1 kHz 1.0Vrms                                   |
| Capacitance Tolerance  | 10%   |
| Voltage DC   | 3000 VDC  |
| Dielectric Withstanding Voltage                                    | 3600 VDC  |
| Temperature Range  | -55/+125°C                                      |
| Temperature Coefficient  | X7R   |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 15%, 1kHz 1.0Vrms                               |
| Dissipation Factor   | 2.5% 1kHz 1.0Vrms                               |
| Aging Rate   | 3% Loss/Decade Hour: Referee Time is 1000 Hours |
| Insulation Resistance  | 100 GOhms                                       |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.