


## C1812X332KFRALTU

Aliases (C1812X332KFRAL7800)

SMD Comm X7R HV Flex, Ceramic, 3300 pF, 10%, 1500 VDC, X7R, SMD, MLCC, FT-CAP, Temperature Stable, 1812



Click [here](#) for the 3D model.

### General Information

|                          |  |
|--------------------------|--|
| Series                   | SMD Comm X7R HV Flex   |
| Style                    | SMD Chip   |
| Description              | SMD, MLCC, FT-CAP, Temperature Stable  |
| Features                 | FT-CAP, Temperature Stable   |
| RoHS                     | No   |
| Prop 65                  | <b>⚠ WARNING:</b> Cancer and reproductive harm - <a href="http://www.p65warnings.ca.gov">http://www.p65warnings.ca.gov</a> . |
| Termination              | Flexible Termination With Lead (SnPb)  |
| Marking                  | false  |
| AEC-Q200                 | No   |
| Typical Component Weight | 95 mg  |
| Shelf Life               | 78 Weeks   |
| MSL                      | 1  |

### Dimensions

|           |                 |
|-----------|-----------------|
| Chip Size | 1812            |
| L         | 4.5mm +/-0.4mm  |
| W         | 3.2mm +/-0.3mm  |
| T         | 1.4mm +/-0.15mm |
| S         | 2.3mm MIN       |
| B         | 0.7mm +/-0.35mm |

### Packaging Specifications

|                    |                          |
|--------------------|--------------------------|
| Packaging          | T&R, 180mm, Plastic Tape |
| Packaging Quantity | 1000                     |

### Specifications

|  |   |
|--|---|
| Capacitance  | 3300 pF   |
| Measurement Condition  | 1 kHz 1.0Vrms                                   |
| Capacitance Tolerance  | 10%   |
| Voltage DC   | 1500 VDC  |
| Dielectric Withstanding Voltage                                    | 1800 VDC  |
| Temperature Range  | -55/+125°C                                      |
| Temperature Coefficient  | X7R   |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 15%, 1kHz 1.0Vrms                               |
| Dissipation Factor   | 2.5% 1kHz 1.0Vrms                               |
| Aging Rate   | 3% Loss/Decade Hour: Referee Time is 1000 Hours |
| Insulation Resistance  | 100 GOhms                                       |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.