
C284ACR4300AL0J







Click here for the 3D model.

Dimensions

Packaging Quantity

C28
Film/Foil Polypropylene
Can
Plastic Case and Cover, Ultra Sonically Welded Seal
Ultra Sonically Welded Seal, Safety Class S3, UL_94 V0 Disk
Yes
Tin Copper
Cables
UL, VDE, UL (Construction Only), UL_94 V0 Disk
No
27 g

D	25mm +1mm
L	55mm +/-2mm
Packaging Specifications	
rackaging specifications	
Terminal Type	Bolt-M8x12

162

Specifications	
Capacitance	3 uF
Tolerance	5%
Voltage AC	470 VAC
Temperature Range	-25/+85°C
Rated Temperature	85°C
Max dV/dt	20 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

Generated 12/04/2025 © 2006 - 2025 YAGEO